



★ NK55/35-XL

Needle roller bearing

Schaeffler ID:
0507544160000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,003 kg	Weight

Main Dimensions & Performance Data

F_w	55 mm	Under roller diameter
D	68 mm	Outside diameter
C	35 mm	Width, outer ring
C_r	60.000 N	Basic dynamic load rating, radial
C_{0r}	118.000 N	Basic static load rating, radial
C_{ur}	21.600 N	Fatigue load limit, radial
n_G	8.400 1/min	Limiting speed
n_{gr}	5.200 1/min	Reference speed

Dimensions

r_{\min}	0,6 mm	Minimum chamfer dimension
------------	--------	---------------------------