



★ NK6/10-TV-XL

Needle roller bearing

Schaeffler ID:
0507526180000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	4,68 g	Weight

Main Dimensions & Performance Data

F_w	6 mm	Under roller diameter
D	12 mm	Outside diameter
C	10 mm	Width, outer ring
C_r	2.950 N	Basic dynamic load rating, radial
C_{0r}	2.280 N	Basic static load rating, radial
C_{ur}	360 N	Fatigue load limit, radial
n_G	36.500 1/min	Limiting speed
n_{gr}	48.500 1/min	Reference speed

Dimensions

r_{\min}	0,15 mm	Minimum chamfer dimension
------------	---------	---------------------------

Additional information

	GR6X12X2	Sealing ring
--	----------	--------------