



## ★ NKI55/35-XL

Needle roller bearing



Schaeffler ID:  
0507624600000

Needle roller bearings NKI, light series

★ Preferred product

X-life

### Technical information



#### Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	0,38 kg	Weight

#### Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	72 mm	Outside diameter
B	35 mm	Width
$C_r$	63.000 N	Basic dynamic load rating, radial
$C_{0r}$	130.000 N	Basic static load rating, radial
$C_{ur}$	23.900 N	Fatigue load limit, radial
$n_G$	7.700 1/min	Limiting speed
$n_{gr}$	4.550 1/min	Reference speed

#### Dimensions

F	60 mm	Raceway diameter inner ring
$r_{\min}$	0,6 mm	Minimum chamfer dimension
s	2 mm	Axial displacement