



★ NKS60-XL

Needle roller bearing

Schaeffler ID:
0507700980000

Needle roller bearings NKS, heavy series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,003 kg	Weight

Main Dimensions & Performance Data

F_w	60 mm	Under roller diameter
D	80 mm	Outside diameter
C	28 mm	Width, outer ring
C_r	71.000 N	Basic dynamic load rating, radial
C_{0r}	98.000 N	Basic static load rating, radial
C_{ur}	17.600 N	Fatigue load limit, radial
n_G	7.400 1/min	Limiting speed
n_{gr}	4.750 1/min	Reference speed

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
------------	--------	---------------------------