

**NKS75-XL**

Needle roller bearing

Schaeffler ID:
0507701440000

Needle roller bearings NKS, heavy series

X-life

Technical information

**Temperature range**

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,401 kg	Weight

Main Dimensions & Performance Data

F_w	75 mm	Under roller diameter
D	95 mm	Outside diameter
C	28 mm	Width, outer ring
C_r	81.000 N	Basic dynamic load rating, radial
C_{0r}	123.000 N	Basic static load rating, radial
C_{ur}	22.200 N	Fatigue load limit, radial
n_G	6.000 1/min	Limiting speed
n_{gr}	3.950 1/min	Reference speed

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
------------	--------	---------------------------