

★ RNA4824-XL

Radial roller bearing


Schaeffler ID:
0507673130000

Radial roller bearing RNA..-XL

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,73 kg	Weight

Main Dimensions & Performance Data

F_w	130 mm	Under roller diameter
D	150 mm	Outside diameter
B	30 mm	Width
C_r	112.000 N	Basic dynamic load rating, radial
C_{0r}	239.000 N	Basic static load rating, radial
C_{ur}	39.500 N	Fatigue load limit, radial
n_G	3.600 1/min	Limiting speed
$n_{G \text{ Grease}}$	2.160 1/min	Limiting speed for grease lubrication
n_{gr}	2.120 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
C	30 mm	Width, outer ring