



★ RNA4915-XL

Radial roller bearing

Schaeffler ID:
0506664870000

Radial roller bearing RNA..-XL

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,005 kg	Weight

Main Dimensions & Performance Data

F_w	85 mm	Under roller diameter
D	105 mm	Outside diameter
B	30 mm	Width
C_r	97.000 N	Basic dynamic load rating, radial
C_{0r}	162.000 N	Basic static load rating, radial
C_{ur}	29.000 N	Fatigue load limit, radial
n_G	5.400 1/min	Limiting speed
$n_{G \text{ Grease}}$	3.200 1/min	Limiting speed for grease lubrication
n_{gr}	3.200 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
C	30 mm	Width, outer ring