**RNA4920-XL**


Radial roller bearing

Schaeffler ID:
0506729160000

Radial roller bearing RNA..-XL

X-life

Technical information

**Main Dimensions & Performance Data**

F_w	115 mm	Under roller diameter
D	140 mm	Outside diameter
B	40 mm	Width
C_r	144.000 N	Basic dynamic load rating, radial
C_{0r}	270.000 N	Basic static load rating, radial
C_{ur}	46.000 N	Fatigue load limit, radial
n_G	4.000 1/min	Limiting speed
$n_{G \text{ Grease}}$	2.400 1/min	Limiting speed for grease lubrication
n_{gr}	2.650 1/min	Reference speed
	0,012 kg	Weight

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
C	40 mm	Width, outer ring

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.