



## ★ AXK120155-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000358239065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	120 mm	Bore diameter cage
$D_c$	155 mm	Outside diameter
$D_w$	4 mm	Rolling element diameter
$E_a$	153 mm	Raceway dimension
$E_b$	125 mm	Raceway dimension
$c_a$	102.000 N	Basic dynamic load rating, axial
$c_{0a}$	680.000 N	Basic static load rating, axial
$c_{ua}$	69.000 N	Fatigue load limit, axial
$n_G$	2.090 1/min	Limiting speed
$n_{gr}$	810 N	Reference speed
	0,001 kg	Weight

#### Additional information

AS120155	Axial bearing washer
----------	----------------------

