



## ★ AXK130170-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000358669065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	130 mm	Bore diameter cage
$D_c$	170 mm	Outside diameter
$D_w$	5 mm	Rolling element diameter
$E_a$	167 mm	Raceway dimension
$E_b$	136 mm	Raceway dimension
$c_a$	134.000 N	Basic dynamic load rating, axial
$c_{0a}$	840.000 N	Basic static load rating, axial
$c_{ua}$	77.000 N	Fatigue load limit, axial
$n_G$	1.920 1/min	Limiting speed
$n_{gr}$	760 N	Reference speed
	0,002 kg	Weight

#### Additional information

AS130170	Axial bearing washer
----------	----------------------

