



★ AXK1528-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000352209065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	15 mm	Bore diameter cage
D_c	28 mm	Outside diameter
D_w	2 mm	Rolling element diameter
E_a	27 mm	Raceway dimension
E_b	17 mm	Raceway dimension
c_a	11.400 N	Basic dynamic load rating, axial
c_{0a}	36.000 N	Basic static load rating, axial
c_{ua}	3.650 N	Fatigue load limit, axial
n_G	13.400 1/min	Limiting speed
n_{gr}	5.100 N	Reference speed
	3,709 g	Weight

Additional information

AS1528	Axial bearing washer
--------	----------------------

