



★ AXK160200-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000359639065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	160 mm	Bore diameter cage
D_c	200 mm	Outside diameter
D_w	5 mm	Rolling element diameter
E_a	197 mm	Raceway dimension
E_b	166 mm	Raceway dimension
c_a	148.000 N	Basic dynamic load rating, axial
c_{0a}	1.020.000 N	Basic static load rating, axial
c_{ua}	88.000 N	Fatigue load limit, axial
n_G	1.600 1/min	Limiting speed
n_{gr}	620 N	Reference speed
	0,002 kg	Weight

Additional information

AS160200	Axial bearing washer
----------	----------------------

