



★ AXK2035-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000352979065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	20 mm	Bore diameter cage
D_c	35 mm	Outside diameter
D_w	2 mm	Rolling element diameter
E_a	34 mm	Raceway dimension
E_b	22 mm	Raceway dimension
c_a	13.100 N	Basic dynamic load rating, axial
c_{0a}	46.500 N	Basic static load rating, axial
c_{ua}	4.800 N	Fatigue load limit, axial
n_G	10.500 1/min	Limiting speed
n_{gr}	4.350 N	Reference speed
	5,4 g	Weight

Additional information

AS2035	Axial bearing washer
--------	----------------------

