



★ AXK5578-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000356029065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D _{c1}	55 mm	Bore diameter cage
D _c	78 mm	Outside diameter
D _w	3 mm	Rolling element diameter
E _a	76 mm	Raceway dimension
E _b	60 mm	Raceway dimension
c _a	38.500 N	Basic dynamic load rating, axial
c _{0a}	186.000 N	Basic static load rating, axial
c _{ua}	20.700 N	Fatigue load limit, axial
n _G	4.350 1/min	Limiting speed
n _{gr}	1.780 N	Reference speed
	27,016 g	Weight

Additional information

AS5578	Axial bearing washer
--------	----------------------

