



★ AXK6085-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000356299065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	60 mm	Bore diameter cage
D_c	85 mm	Outside diameter
D_w	3 mm	Rolling element diameter
E_a	83 mm	Raceway dimension
E_b	65 mm	Raceway dimension
c_a	45.000 N	Basic dynamic load rating, axial
c_{0a}	234.000 N	Basic static load rating, axial
c_{ua}	27.000 N	Fatigue load limit, axial
n_G	3.950 1/min	Limiting speed
n_{gr}	1.590 N	Reference speed
	32,962 g	Weight

Additional information

AS6085	Axial bearing washer
--------	----------------------

