



## ★ AXK6590-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000356539065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	65 mm	Bore diameter cage
$D_c$	90 mm	Outside diameter
$D_w$	3 mm	Rolling element diameter
$E_a$	88 mm	Raceway dimension
$E_b$	70 mm	Raceway dimension
$c_a$	47.000 N	Basic dynamic load rating, axial
$c_{0a}$	255.000 N	Basic static load rating, axial
$c_{ua}$	29.000 N	Fatigue load limit, axial
$n_G$	3.700 1/min	Limiting speed
$n_{gr}$	1.470 N	Reference speed
	35,38 g	Weight

#### Additional information

AS6590	Axial bearing washer
--------	----------------------

