



## ★ AXK7095-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000356889065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	70 mm	Bore diameter cage
$D_c$	95 mm	Outside diameter
$D_w$	4 mm	Rolling element diameter
$E_a$	93 mm	Raceway dimension
$E_b$	74 mm	Raceway dimension
$c_a$	54.000 N	Basic dynamic load rating, axial
$c_{0a}$	255.000 N	Basic static load rating, axial
$c_{ua}$	27.000 N	Fatigue load limit, axial
$n_G$	3.500 1/min	Limiting speed
$n_{gr}$	1.430 N	Reference speed
	49,15 g	Weight

#### Additional information

AS7095	Axial bearing washer
--------	----------------------

