



★ AXK75100-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000357009065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	75 mm	Bore diameter cage
D_c	100 mm	Outside diameter
D_w	4 mm	Rolling element diameter
E_a	98 mm	Raceway dimension
E_b	79 mm	Raceway dimension
c_a	55.000 N	Basic dynamic load rating, axial
c_{0a}	265.000 N	Basic static load rating, axial
c_{ua}	28.500 N	Fatigue load limit, axial
n_G	3.300 1/min	Limiting speed
n_{gr}	1.350 N	Reference speed
	51,76 g	Weight

Additional information

AS75100	Axial bearing washer
---------	----------------------

