



★ LR20X25X12,5


Inner ring

Schaeffler ID:
0000599190000

Inner ring LR, cylindrical

★ Preferred product

Technical information



Main Dimensions & Performance Data

d	20 mm	Bore diameter
F	25 mm	Raceway diameter inner ring
B	12,5 mm	Width
r _{min}	0,3 mm	Minimum chamfer dimension
	30 °	Chamfer angle
	0,017 kg	Weight