



GRA25-XL



Flanged housing unit

Schaeffler ID:
0008293820000

Housing units GRA, three/four-bolt flanged housing units, sheet steel, eccentric locking collar, P seals

X-life

Technical information



Main Dimensions & Performance Data

d	25 mm	Bore diameter
H	95 mm	Height flange
H	95 mm	Flange width
U	25,5 mm	Total height unit
B ₁	31 mm	Locking collar total width
C _{ur}	410 N	Fatigue load limit, radial
C _r	14.900 N	Basic dynamic load rating, radial
C _{0r}	7.800 N	Basic static load rating, radial
C _{0rG}	3.650 N	Load carrying capacity (housing)
	0,34 kg	Weight

Dimensions

A	8,7 mm	Height housing
	1	Number of housings
	1	Number of housings 2
	FLAN52-MSB	Housing
	FLAN52-MSA	Housing (Part 2)
	EXZ	Fixing
	GRAE25-XL-NPP-B	Bearing designation
S	2 mm	Thickness of flange
V	60 mm	Shoulder diameter housing
d ₃	37,5 mm	Outside diameter eccentric locking collar
d ₃	37,5 mm	Outside diameter locking collar/locknut

Mounting dimensions

J	76 mm	Pitch circle diameter (holes)
N	8,7 mm	Fixing square
n	3	Number of screwing holes
n	3	Number of screws