



## ★ PCSLT20-XL

Flanged housing unit

Schaeffler ID:  
0009748380000

★ Preferred product

Housing units PCSLT, two-bolt flanged housing units, sheet steel, eccentric locking collar, P seals

X-life

### Technical information

#### Main Dimensions & Performance Data

d	20 mm	Bore diameter
L	66 mm	Flange width
H	90,5 mm	Height flange
U	26,1 mm	Total height unit
C <sub>r</sub>	9.400 N	Basic dynamic load rating, radial
C <sub>0r</sub>	5.000 N	Basic static load rating, radial
C <sub>0rG</sub>	4.200 N	Load carrying capacity (housing)
	0,2 kg	Weight

#### Dimensions

A	14 mm	Height housing
A <sub>2</sub>	7,5 mm	Distance raceway
S <sub>1</sub>	3 mm	Thickness
S	2 mm	Thickness of flange

#### Mounting dimensions

J	71,4 mm	Distance fixing bore
N	8,7 mm	Fixing square
n	2	Number of screwing holes

#### Additional information

	1	Number of housings
	1	Number of housings 2
	FLAN42-CSLT	Housing
	FLAN42-CST	Housing (Part 2)
	RALE20-XL-NPP-B	Bearing designation