



★ PCSLT25-XL

Flanged housing unit

Schaeffler ID:
0009748620000

★ Preferred product

Housing units PCSLT, two-bolt flanged housing units, sheet steel, eccentric locking collar, P seals

X-life

Technical information

Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	71 mm	Flange width
H	95,2 mm	Height flange
U	28 mm	Total height unit
C _r	10.100 N	Basic dynamic load rating, radial
C _{0r}	5.900 N	Basic static load rating, radial
C _{0rG}	4.500 N	Load carrying capacity (housing)
	0,25 kg	Weight

Dimensions

A	16 mm	Height housing
A ₂	8,5 mm	Distance raceway
S ₁	3 mm	Thickness
S	2 mm	Thickness of flange

Mounting dimensions

J	76,2 mm	Distance fixing bore
N	8,7 mm	Fixing square
n	2	Number of screwing holes

Additional information

	1	Number of housings
	1	Number of housings 2
	FLAN47-CSLT	Housing
	FLAN47-CST	Housing (Part 2)
	RALE25-XL-NPP-B	Bearing designation