



★ RCJY25-XL-N

Flanged housing unit



Schaeffler ID:
0008674460000

Housing units RCJY, four-bolt flanged housing units, cast iron, grub screws in inner ring, R seals

★ Preferred product

X-life

Technical information



Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	95 mm	Flange width
U	38,8 mm	Total height unit
C_r	14.000 N	Basic dynamic load rating, radial
C_{0r}	7.800 N	Basic static load rating, radial
C_{ur}	335 N	Fatigue load limit, radial
	0,76 kg	Weight

Dimensions

A	29 mm	Height housing
A_1	11 mm	Thickness of flange
A_2	19 mm	Distance raceway
B	34,1 mm	Width
V	74 mm	Shoulder diameter housing
Q	M6	Connection thread lubrication

Mounting dimensions

J	70 mm	Distance fixing bore
N	11.5 mm	Fixing bore
n	4	Number of screwing holes

Additional information

1	Number of housings
CJ05	Housing
GYE25-XL-KRR-B	Bearing designation
KASK05	Protecting cap