



IMAGE
COMING SOON



LR5304-2HRS-TVH-XL

Track roller

Schaeffler ID:
0838744100000

Track rollers LR50, double row, sealed on both sides

X-life

Technical information

Main Dimensions & Performance Data

D	62 mm	Outside diameter
d	20 mm	Bore diameter
C	22,2 mm	Height
$C_{r w}$	22.200 N	Basic dynamic load rating, radial
$C_{0r w}$	17.200 N	Basic static load rating, radial
$C_{ur w}$	860 N	Fatigue load limit, radial
n_{DG}	4.850 1/min	Speed on permanent grease lubrication
$F_{r per}$	17.200 N	Permissible dynamic load outer ring, radial
	0,34 kg	Weight

Dimensions

d_2	31,9 mm	Diameter of thrust washer
r_{min}	1,1 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile