



IMAGE
COMING SOON



★ LR5305-2HRS-TVH-XL

Track roller

Schaeffler ID:
0838747630000

Track rollers LR50, double row, sealed on both sides

★ Preferred product

X-life

Technical information

Main Dimensions & Performance Data

D	72 mm	Outside diameter
d	25 mm	Bore diameter
C	25,4 mm	Height
C _{r w}	28.000 N	Basic dynamic load rating, radial
C _{0r w}	22.500 N	Basic static load rating, radial
C _{ur w}	1.140 N	Fatigue load limit, radial
n _{D G}	4.100 1/min	Speed on permanent grease lubrication
F _{r per}	22.500 N	Permissible dynamic load outer ring, radial
	0,5 kg	Weight

Dimensions

d ₂	37,6 mm	Diameter of thrust washer
r _{min}	1,1 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile