

★ NA2205-2RSR


Yoke type track roller

Schaeffler ID:
0007032300000

★ Preferred product

Yoke type track rollers NA22...-2RSR,
without axial guidance, lip seals on both
sides

Technical information



Main Dimensions & Performance Data

D	52 mm	Outside diameter
F	30 mm	Raceway diameter inner ring
C	17,8 mm	Width, outer ring
$C_{r w}$	14.400 N	Basic dynamic load rating, radial
$C_{0r w}$	21.100 N	Basic static load rating, radial
$C_{ur w}$	2.950 N	Fatigue load limit, radial
n_{DG}	1.800 1/min	Speed on permanent grease lubrication
	0,209 kg	Weight

Dimensions

d	25 mm	Bore diameter
B	18 mm	Width, inner ring
$D_{1 \min}$	38 mm	Minimum mounting dimension
r_{\min}	1 mm	Minimum chamfer dimension
$r_{1 \min}$	0,3 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile