



★ K8X11X13-TV


Needle roller cage assembly

Schaeffler ID:
0000241556063

Needle roller cage assembly K...-TV, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-20 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	1,71 g	Weight

Main Dimensions & Performance Data

F_w	8 mm	Inner diameter of needle roller complement
E_w	11 mm	Outside diameter of needle roller complement
B_c	13 mm	Width
C_r	5.100 N	Basic dynamic load rating, radial
C_{0r}	5.800 N	Basic static load rating, radial
C_{ur}	800 N	Fatigue load limit, radial
n_G	32.500 1/min	Limiting speed
n_{gr}	30.500 1/min	Reference speed