



★ K7X10X8-TV

Needle roller cage assembly

Schaeffler ID:
0001567106063

Needle roller cage assembly K...-TV, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-20 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	0,001 kg	Weight

Main Dimensions & Performance Data

F_w	7 mm	Inner diameter of needle roller complement
E_w	10 mm	Outside diameter of needle roller complement
B_c	8 mm	Width
C_r	2.850 N	Basic dynamic load rating, radial
C_{0r}	2.650 N	Basic static load rating, radial
C_{ur}	335 N	Fatigue load limit, radial
n_G	34.500 1/min	Limiting speed
n_{gr}	36.000 1/min	Reference speed