



## ★ K22X30X15-TV

### Needle roller cage assembly

Schaeffler ID:  
0000046426063

Needle roller cage assembly K...-TV, single row

★ Preferred product

## Technical information



### Temperature range

$T_{min}$	-20 °C	Operating temperature min.
$T_{max}$	120 °C	Operating temperature max.
	18,2 g	Weight

### Main Dimensions & Performance Data

$F_w$	22 mm	Inner diameter of needle roller complement
$E_w$	30 mm	Outside diameter of needle roller complement
$B_c$	15 mm	Width
$C_r$	20.100 N	Basic dynamic load rating, radial
$C_{0r}$	23.400 N	Basic static load rating, radial
$C_{ur}$	3.100 N	Fatigue load limit, radial
$n_G$	18.800 1/min	Limiting speed
$n_{gr}$	10.200 1/min	Reference speed