

★ KSR20-B0-16-10-10-15


Roller chain idler sprocket unit

Schaeffler ID:
0008341650000

Roller chain idler sprocket units KSR...B0,
sprocket made from steel or sintered iron

★ Preferred product

Technical information



Main Dimensions & Performance Data

d	20 mm	Bore diameter
d	0,018 mm	Upper tolerance
d	0 mm	Lower tolerance
C ₁	15,3 mm	Thickness of sprocket
D ₀	82,3 mm	Pitch circle diameter (gearing)
D _k	89,4 mm	Tip diameter (gearing)
	0,45 kg	Weight

Dimensions

C ₂	2 mm	Chamfer width
D	47 mm	Outside diameter
B ₁	31 mm	Locking collar total width
C	14 mm	Width, outer ring
d ₃	33 mm	Outside diameter locking collar/locknut
d ₃	33 mm	Outside diameter eccentric locking collar
W	3 mm	Width of flats
B ₁	31 mm	Locking collar width

Mounting dimensions

p	1 Inch	Tooth set
z	10	Number of teeth
	x	ISO chain
W	M6 X 0,75 mm	Width accros flats