

## ★ NATR30


Yoke type track roller

Schaeffler ID:  
0000319840000

Yoke type track rollers NATR, with axial guidance, gap seals on both sides

★ Preferred product

### Technical information



#### Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	62 mm	Outside diameter
B	29 mm	Width, inner ring
$C_{r w}$	23.200 N	Basic dynamic load rating, radial
$C_{0r w}$	39.500 N	Basic static load rating, radial
$C_{ur w}$	5.300 N	Fatigue load limit, radial
$n_{DG}$	1.300 1/min	Speed on permanent grease lubrication
$F_{0r per}$	39.500 N	Permissible static load, radial
$F_{r per}$	39.500 N	Permissible dynamic load outer ring, radial
	0,005 kg	Weight

#### Dimensions

C	28 mm	Width, outer ring
$d_2$	51 mm	Outside diameter of thrust washer
$r_{min}$	1 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile