

★ NUTR40


Yoke type track roller

Schaeffler ID:
0095960970000

★ Preferred product

Yoke type track rollers NUTR, full complement cylindrical roller set, with axial guidance, labyrinth seals on both sides

Technical information



Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	32 mm	Width, inner ring
$C_{r w}$	56.000 N	Basic dynamic load rating, radial
$C_{0r w}$	81.000 N	Basic static load rating, radial
$C_{ur w}$	11.300 N	Fatigue load limit, radial
n_{DG}	1.600 1/min	Speed on permanent grease lubrication
$F_{0r per}$	60.000 N	Permissible static load, radial
$F_{r per}$	31.000 N	Permissible dynamic load outer ring, radial
	0,816 kg	Weight

Dimensions

C	30 mm	Width, outer ring
d_2	50,5 mm	Stop diameter of thrust washer
r_{min}	1,1 mm	Minimum chamfer dimension
$r_{1 min}$	0,6 mm	Minimum chamfer dimension