



★ PSFT25-XL

Take-up housing unit

Schaeffler ID:
0008565170000

★ Preferred product

Take-up housing units PSFT, cast iron housing, radial insert ball bearing with eccentric locking collar, P seals

X-life

Technical information

Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	124 mm	Length total
U	36 mm	Total height unit
	0,49 kg	Weight

Dimensions

A ₁	11 mm	Thickness of flange
A ₂	12,5 mm	Distance raceway
A	20 mm	Height housing
V	70 mm	Shoulder diameter housing
W	63 mm	Width housing slot side
Q	M6	Connection thread lubrication

Mounting dimensions

N	11.5 mm	Fixing bore
N ₁	37,5 mm	Length (slot)
N ₂	11,5 mm	Width (slot)
J	99 mm	Distance fixing bore

Additional information

SFT05	Housing
GRAE25-XL-NPP-B	Bearing designation