



★ PCSLT30-XL

Flanged housing unit

Schaeffler ID:
0009748970000

★ Preferred product

Housing units PCSLT, two-bolt flanged housing units, sheet steel, eccentric locking collar, P seals

X-life

Technical information

Main Dimensions & Performance Data

d	30 mm	Bore diameter
L	84 mm	Flange width
H	112,5 mm	Height flange
U	29 mm	Total height unit
C _r	13.200 N	Basic dynamic load rating, radial
C _{0r}	8.300 N	Basic static load rating, radial
C _{0rG}	6.000 N	Load carrying capacity (housing)
	0,32 kg	Weight

Dimensions

A	16 mm	Height housing
A ₂	9 mm	Distance raceway
S ₁	3,5 mm	Thickness
S	2,5 mm	Thickness of flange

Mounting dimensions

J	90,5 mm	Distance fixing bore
N	11,5 mm	Fixing square
n	2	Number of screwing holes

Additional information

	1	Number of housings
	1	Number of housings 2
	FLAN55-CSLT	Housing
	FLAN55-CST	Housing (Part 2)
	RALE30-XL-NPP-B	Bearing designation