



★ RCJTY25-TV-VA

Flanged housing unit

Schaeffler ID:
0517325210000

Flanged housing unit RCJTY...-TV-VA

★ Preferred product

Technical information

Main Dimensions & Performance Data

d	25 mm	Bore diameter
L	70 mm	Flange width
H	130 mm	Height flange
U	36,8 mm	Total height unit
C _r	13.400 N	Basic dynamic load rating, radial
C _{0r}	7.500 N	Basic static load rating, radial
C _{ur}	370 N	Fatigue load limit, radial
C _{0rG}	11.100 N	Load carrying capacity (housing)
	0,309 kg	Weight

Dimensions

A	29,1 mm	Height housing
A ₁	13,5 mm	Thickness of flange
A ₂	17 mm	Distance raceway
B	34,1 mm	Width

Mounting dimensions

J	99 mm	Distance fixing bore
N	11 mm	Fixing bore
W	SW2,5 mm	Width across flats
n	2	Number of screwing holes

Additional information

1	Number of housings
GEHCJT05-TV	Housing
GYE25-XL-KRR-B- FA107-VA	Bearing designation
KASK05	Protecting cap