



★ RCJTY35-TV-VA

Flanged housing unit

Schaeffler ID:
0517325800000

Flanged housing unit RCJTY..-TV-VA

★ Preferred product

Technical information

Main Dimensions & Performance Data

d	35 mm	Bore diameter
L	90 mm	Flange width
H	163 mm	Height flange
U	43,4 mm	Total height unit
C _r	24.600 N	Basic dynamic load rating, radial
C _{0r}	14.600 N	Basic static load rating, radial
C _{ur}	720 N	Fatigue load limit, radial
C _{0rG}	14.900 N	Load carrying capacity (housing)
	0,641 kg	Weight

Dimensions

A	32,8 mm	Height housing
A ₁	16,1 mm	Thickness of flange
A ₂	18 mm	Distance raceway
B	42,9 mm	Width

Mounting dimensions

J	130 mm	Distance fixing bore
N	13 mm	Fixing bore
W	SW3 mm	Width across flats
n	2	Number of screwing holes

Additional information

1	Number of housings
GEHCJT07-TV	Housing
GYE35-XL-KRR-B-FA107-VA	Bearing designation
KASK07	Protecting cap