



★ RCJY30-TV-VA

Flanged housing unit

Schaeffler ID:
0519632210000

Flanged housing unit RCJY...-TV-VA

★ Preferred product

Technical information

Main Dimensions & Performance Data

d	30 mm	Bore diameter
L	107 mm	Flange width
U	41,4 mm	Total height unit
C _r	18.700 N	Basic dynamic load rating, radial
C _{0r}	10.700 N	Basic static load rating, radial
C _{ur}	530 N	Fatigue load limit, radial
C _{0rG}	17.700 N	Load carrying capacity (housing)
	0,496 kg	Weight

Dimensions

A	31,5 mm	Height housing
A ₁	14,3 mm	Thickness of flange
A ₂	19,2 mm	Distance raceway
B	38,1 mm	Width

Mounting dimensions

J	83 mm	Distance fixing bore
N	11 mm	Fixing bore
W	SW3 mm	Width across flats
n	4	Number of screwing holes

Additional information

1	Number of housings
GEHCJ06-TV	Housing
GYE30-KRR-B-FA107- VA	Bearing designation
KASK06	Protecting cap