



★ AXK1226-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000351739065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	12 mm	Bore diameter cage
D_c	26 mm	Outside diameter
D_w	2 mm	Rolling element diameter
E_a	25 mm	Raceway dimension
E_b	14 mm	Raceway dimension
c_a	9.900 N	Basic dynamic load rating, axial
c_{0a}	29.000 N	Basic static load rating, axial
c_{ua}	2.950 N	Fatigue load limit, axial
n_G	15.200 1/min	Limiting speed
n_{gr}	6.500 N	Reference speed
	3,456 g	Weight

Additional information

AS1226	Axial bearing washer
--------	----------------------

