



## ★ AXK1528-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000352209065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	15 mm	Bore diameter cage
$D_c$	28 mm	Outside diameter
$D_w$	2 mm	Rolling element diameter
$E_a$	27 mm	Raceway dimension
$E_b$	17 mm	Raceway dimension
$c_a$	11.400 N	Basic dynamic load rating, axial
$c_{0a}$	36.000 N	Basic static load rating, axial
$c_{ua}$	3.650 N	Fatigue load limit, axial
$n_G$	13.400 1/min	Limiting speed
$n_{gr}$	5.100 N	Reference speed
	3,709 g	Weight

#### Additional information

AS1528	Axial bearing washer
--------	----------------------

