



★ AXK1730-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000352549065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	17 mm	Bore diameter cage
D_c	30 mm	Outside diameter
D_w	2 mm	Rolling element diameter
E_a	29 mm	Raceway dimension
E_b	19 mm	Raceway dimension
c_a	12.000 N	Basic dynamic load rating, axial
c_{0a}	39.500 N	Basic static load rating, axial
c_{ua}	4.000 N	Fatigue load limit, axial
n_G	12.300 1/min	Limiting speed
n_{gr}	4.600 N	Reference speed
	4,109 g	Weight

Additional information

AS1730	Axial bearing washer
--------	----------------------

