



★ AXK6590-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000356539065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	65 mm	Bore diameter cage
D_c	90 mm	Outside diameter
D_w	3 mm	Rolling element diameter
E_a	88 mm	Raceway dimension
E_b	70 mm	Raceway dimension
c_a	47.000 N	Basic dynamic load rating, axial
c_{0a}	255.000 N	Basic static load rating, axial
c_{ua}	29.000 N	Fatigue load limit, axial
n_G	3.700 1/min	Limiting speed
n_{gr}	1.470 N	Reference speed
	35,38 g	Weight

Additional information

AS6590	Axial bearing washer
--------	----------------------

