



★ AXK7095-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000356889065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D _{c1}	70 mm	Bore diameter cage
D _c	95 mm	Outside diameter
D _w	4 mm	Rolling element diameter
E _a	93 mm	Raceway dimension
E _b	74 mm	Raceway dimension
c _a	54.000 N	Basic dynamic load rating, axial
c _{0a}	255.000 N	Basic static load rating, axial
c _{ua}	27.000 N	Fatigue load limit, axial
n _G	3.500 1/min	Limiting speed
n _{gr}	1.430 N	Reference speed
	49,15 g	Weight

Additional information

AS7095	Axial bearing washer
--------	----------------------

