



## ★ AXK90120-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000357699065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	90 mm	Bore diameter cage
$D_c$	120 mm	Outside diameter
$D_w$	4 mm	Rolling element diameter
$E_a$	118 mm	Raceway dimension
$E_b$	94 mm	Raceway dimension
$c_a$	73.000 N	Basic dynamic load rating, axial
$c_{0a}$	405.000 N	Basic static load rating, axial
$c_{ua}$	45.500 N	Fatigue load limit, axial
$n_G$	2.750 1/min	Limiting speed
$n_{gr}$	1.120 N	Reference speed
	73,673 g	Weight

#### Additional information

AS90120	Axial bearing washer
---------	----------------------

