



★ AXK120155-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000358239065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	120 mm	Bore diameter cage
D_c	155 mm	Outside diameter
D_w	4 mm	Rolling element diameter
E_a	153 mm	Raceway dimension
E_b	125 mm	Raceway dimension
c_a	102.000 N	Basic dynamic load rating, axial
c_{0a}	680.000 N	Basic static load rating, axial
c_{ua}	69.000 N	Fatigue load limit, axial
n_G	2.090 1/min	Limiting speed
n_{gr}	810 N	Reference speed
	0,001 kg	Weight

Additional information

AS120155	Axial bearing washer
----------	----------------------

