



★ AXK140180-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:
0000359049065

Axial needle roller and cage assemblies,
single direction, to DIN 5405-2

★ Preferred product

Technical information

Main Dimensions & Performance Data

D_{c1}	140 mm	Bore diameter cage
D_c	180 mm	Outside diameter
D_w	5 mm	Rolling element diameter
E_a	177 mm	Raceway dimension
E_b	146 mm	Raceway dimension
c_a	139.000 N	Basic dynamic load rating, axial
c_{0a}	900.000 N	Basic static load rating, axial
c_{ua}	81.000 N	Fatigue load limit, axial
n_G	1.800 1/min	Limiting speed
n_{gr}	710 N	Reference speed
	0,002 kg	Weight

Additional information

AS140180	Axial bearing washer
----------	----------------------

