



## ★ AXK160200-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000359639065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	160 mm	Bore diameter cage
$D_c$	200 mm	Outside diameter
$D_w$	5 mm	Rolling element diameter
$E_a$	197 mm	Raceway dimension
$E_b$	166 mm	Raceway dimension
$c_a$	148.000 N	Basic dynamic load rating, axial
$c_{0a}$	1.020.000 N	Basic static load rating, axial
$c_{ua}$	88.000 N	Fatigue load limit, axial
$n_G$	1.600 1/min	Limiting speed
$n_{gr}$	620 N	Reference speed
	0,002 kg	Weight

#### Additional information

AS160200	Axial bearing washer
----------	----------------------

