



★ KH25

Linear ball bearing

Schaeffler ID:
0000450200000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	25 mm	Diameter shaft
D	35 mm	Outer diameter
L	40 mm	Länge
C_{min}	2.280 N	load capacity dyn.
C_{0min}	1.670 N	load capacity stat.
C_{max}	2.420 N	load capacity dyn.
C_{0max}	2.130 N	load capacity stat.
	64 g	Weight

Mounting dimensions

J_{L4}	8 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

