



## ★ AXK4060-A/0-10

Axial needle roller and cage assembly

Schaeffler ID:  
0000591109065

Axial needle roller and cage assemblies,  
single direction, to DIN 5405-2

★ Preferred product

### Technical information

#### Main Dimensions & Performance Data

$D_{c1}$	40 mm	Bore diameter cage
$D_c$	60 mm	Outside diameter
$D_w$	3 mm	Rolling element diameter
$E_a$	58 mm	Raceway dimension
$E_b$	45 mm	Raceway dimension
$c_a$	28.000 N	Basic dynamic load rating, axial
$c_{0a}$	114.000 N	Basic static load rating, axial
$c_{ua}$	12.100 N	Fatigue load limit, axial
$n_G$	5.800 1/min	Limiting speed
$n_{gr}$	2.440 N	Reference speed
	15,983 g	Weight

#### Additional information

AS4060	Axial bearing washer
--------	----------------------

