



## ★ KH06

Linear ball bearing

Schaeffler ID:  
0003421570000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

## Technical information

### Main Dimensions & Performance Data

$F_w$	6 mm	Diameter shaft
D	12 mm	Outer diameter
L	22 mm	Länge
$C_{min}$	340 N	load capacity dyn.
$C_{0min}$	240 N	load capacity stat.
$C_{max}$	390 N	load capacity dyn.
$C_{0max}$	340 N	load capacity stat.
	8,56 g	Weight

### Mounting dimensions

$J_{L4}$	4 mm
$N_2$	2 mm

### Additional information

VMKB_065	KH	Material name
----------	----	---------------

