



★ KH08

Linear ball bearing

Schaeffler ID:
0003421650000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	8 mm	Diameter shaft
D	15 mm	Outer diameter
L	24 mm	Länge
C_{min}	410 N	load capacity dyn.
C_{0min}	280 N	load capacity stat.
C_{max}	475 N	load capacity dyn.
C_{0max}	400 N	load capacity stat.
	11,9 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

